

DEBUG AQUATIC WHEELCHAIR



ORDER ONLINE WWW.DEBUGMOBILITYPRODUCTS.COM

Debug Mobility Products
78 E Nine Mile Rd
Pensacola, FL 32534

850-478-5765
kmdeming@aol.com
www.beachwheelchair.com

Debug AQUATIC
BEACH WHEELCHAIR



The Debug Aquatic Chair is great for pools, waterparks and showers and can even be used as a manual street wheelchair. As a pool wheelchair it can assist in bringing commercial pools with ramps and waterparks into compliance with the new ADA Swimming Pool Guidelines. The interchangeable front axle and sleeves, along with the rear pool suspension, means it only takes a few moments to convert the Debug

- LONG LASTING #316L STAINLESS STEEL FRAME, REMOVEABLE TELESCOPIC LEG REST
- FITS THROUGH A STANDARD ADA DOORWAY
- TUBELESS SOLID CORE TIRES POLYCARBONATE MAG WHEELS ROLL ACROSS GRAVEL
- ALL STAINLESS STEEL AND RUST PROOF AXLE AND FASTENERS
- DUAL STITCHED SLING WITH TENERA 130 THREAD PHIFERTEX PLUS SLING MATERIAL
- RESISTS STRETCHING, MILDEW AND BACTERIA, COLD CRACK AND ULTRAVIOLET DAMAGE
- AND IS MACHINE WASHABLE.

SPECIFICATIONS

SEAT SIZES	ENGLISH (INCH)	METRIC (CM)
Widths	14, 18, 22	36, 46, 56
Depth	17	43
Seat-to-floor height	17 - 21	43 - 53
Backrest height	18	46
Telescope footrest knee to heel	15 - 22	38 - 58
WEIGHTS		
Capacity	250 – 300 lbs	114 – 136 kg
Chair weight	40 – 65 lbs	18 – 30 kg

Manufactured in the USA,
Debug has a 10 year warranty on stainless steel frames and a 30 day money back guarantee.
© Copyright Deming Designs Inc., 2025

ORDER ONLINE WWW.DEBUGMOBILITYPRODUCTS.COM